

Hot Line Tap Clamp, Bronze

By ANDERSON
Catalog # [S1530CC](#)

Overhead Primary Tap, Hot Line Tap Clamp, Bronze, Copper,
Range 0.162 - 0.728 in



*Representative Image

Features

High pressure developed by eyestem, lock washer assures permanent connection.

General

Catalog Number	S1530CC
Material	Bronze
Material - Body	Bronze
Material - Eyebolt	Bronze
Material - Eyestem	Forged Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359054108

Dimensions

Dimensions	2.400 in x 2.400 in x 7.130 in
Height	7.13 in
Length	2.4 in
Weight	1.558 lb
Width	2.4 in

Electrical Ratings

Maximum Current Rating Amps Continuous	Rated for maximum rating of largest tap conductor in range
--	--

Conductor Related

Conductor Diameter (Tap) - Maximum	0.728 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.528 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.528
Conductor Type	Copper

Logistics

Packaging Type	Box
Pallet Quantity	1200

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - CC-25762](#)
- [Specifications - S1530CC](#)