

HUBBELL Power Systems

Hot Line Tap Clamp, Bronze

By ANDERSON
Catalog # [S1540CC](#)

Overhead Primary Tap, Hot Line Tap Clamp, Bronze, Copper,
Range 0.502 - 1.028 in



*Representative Image

Features

High pressure developed by eyestem, lock washer assures permanent connection.

General

Catalog Number	S1540CC
Material	Bronze
Material - Body	Bronze
Material - Eyebolt	Bronze
Material - Eyestem	Forged Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359378532

Dimensions

Dimensions	3.000 in x 3.000 in x 7.750 in
Height	7.75 in
Length	3 in
Weight	1.989 lb
Width	3 in

Electrical Ratings

Maximum Current Rating Amps Continuous	Rated for maximum rating of largest tap conductor in range
--	--

Conductor Related

Conductor Diameter (Tap) - Maximum	1.03 in
Conductor Diameter (Tap) - Minimum	0.528 in
Conductor Diameter - Maximum	0.681 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.681
Conductor Type	Copper

Logistics

Packaging Type	Box
Pallet Quantity	900

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - CC-25762](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-S1540CC-SPEC-EN | REV 6/2024