

HUBBELL Power Systems

Socket Eye

By ANDERSON
Catalog # [SA10513](#)

Socket eyes can be used for connecting conductor clamping devices to ball and socket type insulators



*Representative Image

Features

For use with ANSI class 52-3 & 52-5 insulators

General

| | |
|---------------------------------|-----------------|
| Catalog Number | SA10513 |
| EU RoHS Indicator | No |
| Material | Ductile Iron |
| Material - Pin (Cotter) | Stainless Steel |
| Number of Bolt Holes | 0 |
| Series | SA Series |
| Strength Rating - Ultimate | 30000 lb |
| Strength Rating - Ultimate Body | 0 lb |
| UPC | 096359324669 |

Dimensions

| | |
|-------------------------------------|----------|
| Assembly Rating (Ultimate) | 0 lb |
| Diameter - Bolt | 0 in |
| Diameter - Eye Hole | 0.813 in |
| Diameter - Pin | 0 in |
| Insulator Throat Diameter - Maximum | 0 in |
| Insulator Throat Diameter - Minimum | 0 in |
| Insulator Throat Diameter Range | 0 - 0 |
| Length - Coupling | 2.063 in |
| Length - Pin | 0 in |
| Maximum Adjustment | 0 in |
| Ring Height | 0 in |
| Weight | 1.274 lb |
| Width - Eye | 1.063 in |

Conductor Related

| | |
|------------------------------|------|
| Conductor Diameter - Maximum | 0 in |
| Conductor Spacing | 0 in |

Logistics

Pallet Quantity 1200

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-SA10513-SPEC-EN | REV 6/2024