

HUBBELL Power Systems

Socket Eye

By ANDERSON
Catalog # [SA11](#)

Socket eyes can be used for connecting conductor clamping devices to ball and socket type insulators



*Representative Image

Features

For use with ANSI class 52-3 & 52-5 insulators

General

Catalog Number	SA11
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SA Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359324683

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.063 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.47 lb
Width - Eye	1.125 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 1152

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-SA11-SPEC-EN | REV 6/2024