

Connector, Split Bolt, #6-#2

By ANDERSON  
Catalog # [SBN2](#)



Connector, Split Bolt, #6-#2

General

Bolt Head Type	Hex
Catalog Number	SBN2
Cover Available	No
Inhibitor Loaded	No
Item Type	3C
Material - Body	Copper Alloy
Plated	N
Plating	No
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Split Bolt
UPC	096359373797
UPC 14 Digit GTIN	00963593737978

Dimensions

Bolt Diameter	0.625 in
Dimensions	0.820 in x 0.720 in x 1.540 in
Height	1.54 in
Length	0.82 in
Weight	0.117 lb
Width	0.72 in

Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in

Conductor Diameter (Main) Range	0 - 0
Conductor Diameter (Tap) - Maximum	0.292 in
Conductor Diameter - Maximum	0.292 in
Conductor Diameter - Minimum	0.184 in
Conductor Diameter Range	0.184 - 0.292

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Pallet Quantity	7000 EA
-----------------	---------

Product Assets

- [3D Models - SBN2\\_MODEL-IGES](#)
- [3D Models - SBN2\\_MODEL-PDF](#)
- [3D Models - SBN2\\_MODEL-STEP](#)
- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - 10111018](#)
- [Specifications - SBN2](#)