

Connector, Split Bolt, #2-2/0

By ANDERSON
Catalog # [SBN20](#)

Connector, Split Bolt, #2-2/0



Features

- Has no cable separator.

General

Bolt Head Type	Hex
Cover Available	No
Inhibitor Loaded	No
Item Type	3C
Material - Body	Copper Alloy
Plated	N
Plating	No
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Split Bolt
UPC	096359373810
UPC 12 Digit	963593738104

Dimensions

Bolt Diameter	<ul style="list-style-type: none">• 0.75• 0.875 in
Dimensions	1.063 in x 0.900 in x 1.940 in
Height	1.940 in
Length	1.063 in
Weight	0.180 lb
Width	0.900 in

Conductor Related

Conductor Diameter (Main) Range	0 - 0
Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.292 in
Conductor Diameter Range	0.292 - 0.419

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1
Pallet Quantity	10080

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - 10111018](#)