

Connector, Split Bolt, 2/0-350
MCM

By ANDERSON
Catalog # [SBN350](#)

Connector, Split Bolt, 2/0-350 MCM



Features

- Has no cable separator.

General

Bolt Head Type	Hex
Cover Available	No
Inhibitor Loaded	No
Item Type	4D
Material - Body	Copper Alloy
Plated	N
Plating	No
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Split Bolt
UPC	096359373841
UPC 12 Digit	963593738418

Dimensions

Bolt Diameter	<ul style="list-style-type: none">• 1.000 in• 1.375 in
Weight	0.500 lb

Conductor Related

Conductor Diameter (Main) Range	0 - 0
Conductor Diameter (Tap) - Maximum	0.681 in
Conductor Diameter - Maximum	0.681 in
Conductor Diameter - Minimum	0.414 in
Conductor Diameter Range	0.414 - 0.681

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	80 EA
Pallet Quantity	3840 EA

Product Assets

[Sales Drawings - 10111018](#)

