

Connector, Split Bolt, #8-#4

By ANDERSON
Catalog # [SBN4](#)

Connector, Split Bolt, #8-#4



Features

- Has no cable separator.

General

Bolt Head Type	Hex
Cover Available	No
Inhibitor Loaded	No
Item Type	3C
Material - Body	Copper Alloy
Plated	N
Plating	No
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Split Bolt
UPC	096359373780
UPC 12 Digit	963593737800

Dimensions

Bolt Diameter	<ul style="list-style-type: none">• 0.5• 0.5 in
Dimensions	0.680 in x 0.590 in x 1.200 in
Height	1.200 in
Length	0.680 in
Weight	0.090 lb
Width	0.590 in

Conductor Related

Conductor Diameter (Main) Range	0 - 0
Conductor Diameter (Tap) - Maximum	0.232 in
Conductor Diameter - Maximum	0.232 in
Conductor Diameter - Minimum	0.146 in
Conductor Diameter Range	0.146 - 0.232

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Pallet Quantity	15000 EA
-----------------	----------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - 10111018](#)