

HUBBELL Power Systems

Connector, Split Bolt, 336-500 MCM

By ANDERSON
Catalog # [SBS500](#)

Copper Split Bolt Connector.



Features

Has cable separator included.

General

| | |
|----------------------------------------|-----------------------|
| Bolt Head Type | Hex |
| Bolt Installation Torque (Recommended) | |
| Cover Available | |
| Inhibitor Loaded | |
| Item Type | 4D |
| Material | Copper |
| Material - Body | Copper Alloy |
| Material - Spacer | Copper Alloy |
| Plated | |
| Plating Type | Unplated |
| Product Category | Mechanical Connectors |
| Style | Split Bolt |
| UPC | 096359373759 |
| UPC 12 Digit | 963593737596 |

Dimensions

| | |
|------------------------------|----------|
| Dimension - L Length Overall | |
| mm | |
| Dimension - Thread Size | |
| Dimension - Width mm | |
| Weight | 0.843 lb |

Conductor Related

| | |
|-------------------------------------|---------------|
| Conductor Diameter (Main) - Maximum | .0814 in |
| Conductor Diameter (Main) - Minimum | 0.741 in |
| Conductor Diameter (Main) Range | 0.741 - .0814 |
| Conductor Diameter (Tap) - Maximum | 0.814 in |
| Conductor Diameter (Tap) - Minimum | 0.292 in |
| Conductor Diameter - Maximum | |
| Conductor Diameter - Minimum | |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | |
| Certification - UL Recognized | |
| Certification - cULus | |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------|---------|
| Pallet Quantity | 3960 EA |
|-----------------|---------|

Product Assets

[Sales Drawings - 10111020](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-SBS500-SPEC-EN | REV 6/2024