

HUBBELL Power Systems

Connector, Split Bolt, #8-#6

By ANDERSON
Catalog # [SBS6](#)

Copper Split Bolt Connector.



Features

Has cable separator included.

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	
Cover Available	
Inhibitor Loaded	
Item Type	4D
Material	Copper
Material - Body	Copper Alloy
Material - Spacer	Copper Alloy
Plated	
Plating Type	Unplated
Product Category	Mechanical Connectors
Style	Split Bolt
UPC	096359373681
UPC 12 Digit	963593736810

Dimensions

Bolt Diameter	0.44
Dimension - L Length Overall mm	
Dimension - Thread Size	
Dimension - Width mm	
Weight	0.049 lb

Conductor Related

Conductor Diameter (Main) - Maximum	0.162 in
Conductor Diameter (Main) - Minimum	0.081 in
Conductor Diameter (Main) Range	0.081 - 0.162
Conductor Diameter (Tap) - Maximum	0.162 in
Conductor Diameter (Tap) - Minimum	0.081 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	
Certification - UL Recognized	
Certification - cULus	
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Pallet Quantity	57600 EA
-----------------	----------

Product Assets

[Sales Drawings - 10111020](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-SBS6-SPEC-EN | REV 6/2024