

# HUBBELL

## Power Systems

### Quadrant Strain Clamp - Aluminum

By ANDERSON  
Catalog # [SD185C](#)

For transmission line construction with all aluminum, ACSR or aluminum alloy conductor or for Alumoweld shield wire.



\*Representative Image

#### Features

- "Type SD is designed for single cable
- The Sag Eye Ultimate Strength is 60% of the Ultimate Body Strength without fitting
- Rated slip strength as a % of conductor RBS varies with conductor type, size, and stranding. Minimum slip strength rating on standard strength conductors is 40% RBS (Partial Tension). For many standard strength conductors, minimum slip strength of this clamp series is 60% RBS (Normal Tension). Consult factory for slip strength test data on specific clamp and conductor combinations
- Bolt and Nut may be substituted for clevis pin by adding suffix "BNK" to catalog number. Example: SD185CBNK
- Bolt and clevis pin will be the same diameter
- The "C" suffix indicates the component will come supplied with clevis eye CA1517033
- For Corona Free applications on EHV lines, add suffix "CRF" to catalog number. Example: SD185CCRF"

#### General

Bolt Installation Torque (Recommended)	720 in-lbs
Catalog Number	SD185C
EU RoHS Indicator	No
Fitting Type	Clevis
Material - Body	Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	Aluminum Alloy
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Bolted Deadend - Quadrant
Strength Rating - Ultimate Body	30000 lb
Style	SD
Type	Bolted
U-Bolts	5 in
UPC	096359325376

#### Dimensions

Clamping - Maximum	1.85 in
Clamping - Minimum	1.3 in
Clevis Opening	1.875 in
Diameter - Clevis Pin	1 in
Diameter - Eye Hole	1.5 in
Height	18 in
Length	17 in
Weight	21.854 lb

#### Electrical Ratings

Voltage Application	Standard
---------------------	----------

#### Conductor Related

Clamping Range	1.30- 1.85
Conductor Compatibility	ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91;AAC-Sagebrush-2250-91;AAC-Lupine-2500-91;ACAR-1933-42/19;ACAR-2493-72/19;ACAR-2493-54/37

## Logistics

Pallet Quantity

24

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)

[Literature - Ropes Course Industry Letter \(April 2021\)](#)

[Sales Drawings - SD Product Family](#)

[Video - Bolted Deadend](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-SD185C-SPEC-EN | REV 6/2024