

HUBBELL

Power Systems

Deadend, Quadrant, Spring Loaded, Side open, Single Bolt, AAC, AAAC, ACAR, ACSR, Conductor Range 0.18 - 0.48 in

By ANDERSON
Catalog # [SLQ48N](#)

Deadend, Quadrant, Spring Loaded, Side opening, Single Bolt, #4 (7 STR) - 2/0 (19 STR) AL, #6 (6/1) - 2/0 (6/1) ACSR, Conductor Range 0.19 - 0.48 in, Fitting: None.



*Representative Image

Features

Spring Loaded, side opening keeper for easy installation, Single 1/2" U-Bolt for use with hand or hydraulic tool installation, Replace suffix "N" with "S" for socket or "C" for Clevis fitting options

General

Fitting Type	None
Material	Aluminum Alloy; Steel
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Product Category	Quadrant
Strength Rating - Ultimate	8000 lb
Body	
Style	SLQ
Type	Bolted
U-Bolts	1 in
UPC	096359495260

Dimensions

Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Weight	1.18 lb

Conductor Related

Conductor Diameter - Maximum	0.48
Conductor Diameter - Minimum	0.19
Conductor Diameter Range	0.19 - 0.48

Logistics

Pallet Quantity	675
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Side Loading Quadrant Deadend \(CC-19579\)](#)



A Hubbell brand