

HUBBELL Power Systems

Connector, Parallel Groove

By ANDERSON
Catalog # [ST4](#)

Single Center Bolt Bronze Parallel Groove Connector



*Representative Image

Features

For copper (Cu), Copperweld® (CW), and guy strand (GS) connections

General

Bolt Head Type	Hex w/Sq Shank
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	ST4
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Stainless Steel
Material - Bottom Member	Bronze Alloy
Material - Casting	Bronze Alloy
Material - Hardware	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Single Center Bolt
UPC	096359326021

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in
Dimensions	0.938 in x 1.875 in x 1.500 in
Height	1.5 in
Length	0.938 in
Weight	0.135 lb
Width	1.875 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.562 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.562
Conductor Diameter - Minimum	0.162
Conductor Diameter Range	0.162 - 0.562

Certifications And Compliance

UL Listed No

Logistics

Pallet Quantity 5760

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - C-11339](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-ST4-SPEC-EN | REV 6/2024