

Coupler, Bronze Bolted

By ANDERSON
Catalog # [STC8120253](#)

"Coupler, Tube to Tube, Bronze Bolted, Heavy duty, 3/4" to 3/4" IPS tubes, Material: Castings-Bronze alloy, Hardware-silicon bronze or stainless steel"



*Representative Image

Features

- "furnished with reversible cable caps
- Hex Stops on the casting allows for one-wrench installation"

General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Type	Tube to Cable Couplers
UPC	096359351627

Dimensions

Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	1-1/4 in
Weight	2.744 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
---	-----------------------

Conductor Related

Conductor Diameter (Tap) - Maximum	0.575 in
Conductor Diameter (Tap) - Minimum	0.204 in
Conductor Type	Copper Bus

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4091 \(STC8 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)