

Socket Y-Clevis

By ANDERSON
Catalog # [SYCS3090](#)

"Bolted Cable Spacer EHV(500 KV), Aluminum Conductor-ACSR (M Max.)-2167 (72/7) - 2156 (84/19), Dia. -1.717"-1.762", Material:Caps-Aluminum Alloy, Cross Braces-Aluminum Alloy, Bolts,Nuts and Lock washers-Aluminum alloy, Hardware Retaining Grommet-Neoprene"



*Representative Image

Features

- "Material: Body-Galvanized ductile iron, Hardware-Galvanized steel, Cotter Pin-stainless steel
- For use with ANSI class 52-3 & 52-5 insulators
- Shield nut can be supplied by adding suffix "SN" to catalog"

General

Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Series	SYC Series
Strength Rating - Ultimate	30000 lb
UPC	096359328551
With Sphere Nut	No

Dimensions

Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.281 in
Weight	2.450 lb

Logistics

Pallet Quantity	540
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)