

Trunnion Suspension Clamp AL

By ANDERSON
Catalog # TSC150

Trunnion Suspension Clamp, Aluminum, Aluminum Cable
Clamping range 1.00-1.50 inches, 2,800 lb Ultimate body
strength



*Representative Image

Features

- For Standard Voltage Applications
- Designed for use on tangent suspension spans with horizontal or vertical post insulators
- Keeper is reversible for proper fit on different size conductors

General

Accessory Type	Clamptop Clamp
Bolt Installation Torque (Recommended)	300 in-lbs
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Number of Sheds	1.00-1.50
Product Category	Suspension Clamp
Series	images/Suspension Connectors/connsusp_tsc_s.jpg
Strength Rating - Ultimate Body	2800 lb
Type	Standard Voltage Suspension Clamps
UPC	096359332053
With Anti-Static Springs	No

Dimensions

Angle - Take-Off Maximum	20 °
Diameter - Clamping Hardware	0 in
Dimensions	5.25 in x 3.88 in x 1.5 in
Height	1.5 in
Length	5.25 in
Nominal Guy Wire Size	0 in
Weight	1.088 lb
Width	3.88 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-

54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Brahma-203.2-16/19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;ACAR-653.1-12/7;ACAR-853.7-30/7;ACAR-1024.5-30/7;ACAR-1109-30/7;ACAR-1172-30/7;ACAR-1172-18/19

Logistics

Pallet Quantity	1000
-----------------	------

20/7;ACSR-Oriole-397.5-
30/7;ACSR-Chickadee-397.5-
18/1;ACSR-Brant-397.5-
24/7;ACSR-Ibis-397.5-
26/7;ACSR-Lark-397.5-
30/7;ACSR-Pelican-477-
18/1;ACSR-Flicker-477-
24/7;ACSR-Hawk-477-
26/7;ACSR-Hen-477-
30/7;ACSR-Osprey-556.5-
18/1;ACSR-Parakeet-556.5-
24/7;ACSR-Dove-556.5-
26/7;ACSR-Eagle-556.5-
30/7;ACSR-Peacock-605-
24/7;ACSR-Squab-605-
26/7;ACSR-Kingbird-636-
18/1;ACSR-Swift-636-
36/1;ACSR-Egret-636-
30/19;ACSR-Flamingo-666.6-
24/7;ACSR-Gannet-666.6-
26/7;ACSR-Stilt-715.5-
24/7;ACSR-Starling-715.5-
26/7;ACSR-Redwing-715.5-
30/19;ACSR-Coot-795-
36/1;ACSR-Cuckoo-795-
24/7;ACSR-Drake-795-
26/7;ACSR-Tern-795-
45/7;ACSR-Condor-795-

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Literature - Ropes Course Industry Letter \(April 2021\)](#)

[Sales Drawings - TSC and TSCHT Product Family](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
AN-TSC150-SPEC-EN | REV 9/2023