

HUBBELL

Power Systems

Trunnion Suspension Clamp AL

By ANDERSON
Catalog # [TSC200](#)



For standard voltage applications with AAC, ACSR, or AAAC conductors. Designed for use on tangent suspension spans with horizontal or vertical post insulators. Keeper is reversible for proper fit on different size conductors.

Features

- For Standard Voltage Applications
- Designed for use on tangent suspension spans with horizontal or vertical post insulators
- Keeper is reversible for proper fit on different size conductors

General

Accessory Type	Clamptop Clamp
Bolt Installation Torque (Recommended)	300 in-lbs
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Number of Bolt Holes	0
Number of Sheds	1.50-2.00
Product Category	Suspension Clamp
Series	images/Suspension Connectors/connsusp_tsc_s.jpg
Strength Rating - Ultimate Body	2800 lb
Type	Standard Voltage Suspension Clamps
UPC	096359332091
With Anti-Static Springs	No

Dimensions

Actual Clamp Strand Diameter Range	0 in
Angle - Take-Off Maximum	20 °
Assembly Rating (Ultimate)	0 lb
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Clevis Opening	0 in
Diameter - Bolt	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Pin	0 in
Dimensions	5.25 in x 3.88 in x 2 in
Height	2 in
Length	5.25 in
Length - Pin	0 in
Nominal Guy Wire Size	0 in
Weight	1.333 lb
Width	3.88 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Teal-605-30/19;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;ACSR-Joree-2515-76/19;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Cowslip-2000-91;AAC-Lupine-2500-91;ACAR-739.8-18/19;ACAR-853.7-30/7;ACAR-1024.5-30/7;ACAR-1109-30/7;ACAR-1172-30/7;ACAR-1172-18/19;ACAR-1933-42/19;ACAR-2493-72/19;ACAR-2493-54/37
Conductor Diameter - Maximum	0 in

Logistics

Pallet Quantity	900
Standard Package	25

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - TSC and TSCHT Product Family](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-TSC200-SPEC-EN | REV 6/2024