

Compression Splice VERSAtile™
Minimum Tension

By ANDERSON
Catalog # [VACS750](#)



Minimum Tension versatile Compression Splice for 750 MCM str
AL

*Representative Image

Features

- For AL to AL, AL to CU connections
- AL9CU (90°C Rated)
- UL Listed
- CSA Certified

General

Catalog Number	VACS750
Color Code	Pink
Compression Method	VersaCrimp or Conventional Die Tooling
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359334477

Dimensions

Diameter - Inside	1.028 in
Weight	0.686 lb

Conductor Related

Conductor Compatibility	ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-
-------------------------	---

30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;ACAR-653.1-12/7;ACAR-739.8-18/19

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	Yes

Logistics

Carton Quantity	24
-----------------	----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - VACS Splice Installation Instructions](#)
- [Sales Drawings - VACS_sales_drawing](#)
- [Specifications - VACS750](#)