

HUBBELL Power Systems

Aluminum Compression Terminal for 450 - 500 AL, 397.5 24/7, 26/7, 477 18/1, 36/1 ACSR, 550 - 600 COMPACT

By ANDERSON
Catalog # [VAUL50012](#)



*Representative Image

Aluminum Compression Terminal for 450 - 500 AL, 397.5 24/7, 26/7, 477 18/1, 36/1 ACSR, 550 - 600 COMPACT, 1 HOLE

Features

Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

General

Catalog Number	VAUL50012
Color Code	None
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Plating	No
Style	Impact Extruded
UPC	096359334927

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Hole Size inch	0.500 in
Weight	0.294 lb

Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-
-------------------------	-----------------------------------------------------------------------------------------------------------

336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Brahma-203.2-16/19;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAAC 6201 Alloy-Alliance-246.9-6/18

Conductor Diameter (VersaCrimp) - Maximum	0.814 in
Conductor Diameter (VersaCrimp) - Minimum	0.52 in

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	40
-----------------	----

Product Assets

[Catalogs - Distribution Connectors](#)
[Installation Manuals - VAUL Terminals Installation Procedures](#)
[Sales Drawings - VAULxxx_drawing](#)
[Specifications - VAUL50012](#)