

Compression Splice **VERSA-CRIMP**[®] Full Tension

By ANDERSON
Catalog # [VC50R](#)



Full Tension VersaCrimp Aluminum Compression Splice for AL #2 (7), 1/0 (7) (19), #2 (6/1) (7/1), 1/0 (6/1), 2/0 (6/1), 5005 or AAAC (6201) 123.3 (7), 155.4 (7)

*Representative Image

Features

- VERSA-CRIMP tools only
- One piece design eliminates cutting strands on ACSR
- Can be used with compressed (compact) conductor sizes within the same decimal range

General

Compression Method	VersaCrimp Tooling ONLY VC6-3 or VC6FTSP
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359335597

Dimensions

Length Before Compression	17.25 in
Weight	0.686 lb

Conductor Related

Conductor Compatibility	ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.447 in
Conductor Diameter (VersaCrimp) - Minimum	0.292 in

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - VC410A_drawing](#)