

VERSAtile Aluminum Compression Terminal 600 MCM AL/CU; 1/2" pad bolt diameter; single hole

By ANDERSON
Catalog # [VCEL06012H1](#)



VERSAtile Aluminum Compression Terminal 600 MCM AL/CU; 1/2" pad bolt diameter; single hole

Features

- CSA certified, UL Listed for both concentric and compact aluminum and concentric copper conductor

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336525

Dimensions

Bolt Diameter	0.5
Diameter - Pad Bolt	0.5 in
Weight	0.294 lb

Conductor Related

Conductor Compatibility	ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
-------------------------	--

Conductor Diameter (Die Type Tooling) - Maximum	0.893 in
Conductor Diameter (Die Type Tooling) - Minimum	0.891 in
Conductor Diameter (VersaCrimp) - Maximum	0.893 in
Conductor Diameter (VersaCrimp) - Minimum	0.726 in
Lug Conductor Type	<ul style="list-style-type: none"> • AL • CU

Certifications and Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	48
Pallet Quantity	2880

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VCEL installation instructions](#)
[Sales Drawings - VCEL_drawing](#)
[Sales Drawings - CC-11191](#)

