

HUBBELL Power Systems

900 MCM Compression Splice VERSA-CRIMP®

By ANDERSON
Catalog # [VCJS834R](#)

Partial Tension VersaCrimp Aluminum Compression Splice for
900 (37, 61) AAC, 715 (26/7), 795 (24/7, 26/7, 36/1, 45/7, 54,7)
ACSR



*Representative Image

Features

- For use with VC8 tools only
- Partial tension (40% tension rating) jumping splice
- Can be used with compressed (compact) conductor sizes within the same decimal range

General

Catalog Number	VCJS834R
Compression Method	VersaCrimp Tooling ONLY VC8
Compression Tool Type	VersaCrimp Tooling ONLY VC8
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359336792

Dimensions

Length Before Compression	14.62 in
Weight	2.058 lb

Conductor Related

Conductor Compatibility	ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;ACAR-853.7-30/7
Conductor Diameter (VersaCrimp) - Maximum	1.14 in
Conductor Diameter (VersaCrimp) - Minimum	1.051 in

Certifications And Compliance

UL Listed No

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - VCJS_drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VCJS834R-SPEC-EN | REV 6/2024