

Compression Splice VERSAtile™
Minimum Tension

By ANDERSON
Catalog # [VHS4](#)



Copper long barrel Versatile splice, LNG BARREL #4 STR

*Representative Image

Application

Power Connector

General

Catalog Number	VHS4
Color Code	Gray
Compression Method	VersaCrimp or Conventional Die Tooling
Die Size	VC6-350, VC6350SN
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	No
Material	Copper
Trade Name	NO
UPC	096359338949
UPC 14 Digit GTIN	00096359338949

Dimensions

Length Before Compression	2.38 in
Weight	0.039 lb

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Conductor Related

Conductor Diameter (Conventional Tooling) - Maximum	0.232 in
Conductor Diameter (Conventional Tooling) - Minimum	0.232 in
Conductor Diameter (VersaCrimp) - Maximum	0.232 in
Conductor Diameter (VersaCrimp) - Minimum	0.232 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Carton Quantity	350
Pallet Quantity	25000

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - 50025089](#)
[Specifications - VHS4](#)