

Connector, Parallel Groove

By ANDERSON
Catalog # [XP024024](#)

Two Bolt Bronze Cross Parallel Groove Connector



*Representative Image

Features

- For perpendicular tap and run connections.

General

Bolt Head Type	Hex
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Copper Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two Bolt
UPC	096359353805

Dimensions

Bolt Diameter	0.38
Diameter - Bolt	0.38 in
Weight	0.686 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.528 in
Conductor Diameter (Tap) - Minimum	0.368 in
Conductor Diameter - Maximum	0.528
Conductor Diameter - Minimum	0.368
Conductor Diameter Range	0.368 - 0.528

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	36
Pallet Quantity	1728

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)

Related Products

[XP100100 - Connector, Parallel Groove](#)
[XP050050 - Connector, Parallel Groove](#)
[XP100050 - Connector, Parallel Groove](#)