

Yoke Plate, Crescent

By ANDERSON  
Catalog # [YPC4024534](#)



These yoke plates are used to bundle two conductors with a single and v-string, or single string, of insulators and maintain the proper running angle of the line. Type YPC yoke plates may be furnished in a variety of sizes, hole spacing, ultimate strengths and insulator attachment angles. Material: body - galvanized ductile iron or galvanized steel.

Features

Type YPC yoke plates may be furnished in a variety of sizes, hole spacing, ultimate strengths and insulator attachment angles,Material: Galvanized Ductile Iron

General

Catalog Number	YPC4024534
EU RoHS Indicator	No
Material	Ductile Iron
Number of Bolt Holes	0
Series	YPC Series
Strength Rating - Ultimate	40000 lb
Strength Rating - Ultimate Body	0 lb
Type	Suspension Angle Yokes
UPC	096359344773

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	1.25 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in

Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	7.065 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	6.86 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in
Diameter - Conductor Attachment Holes	1.25 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - YPC4024534](#)