

Yoke Plate, Crescent

By ANDERSON
Catalog # [YPC509378](#)



These yoke plates are used to bundle two conductors with a single and v-string, or single string, of insulators and maintain the proper running angle of the line. Type YPC yoke plates may be furnished in a variety of sizes, hole spacing, ultimate strengths and insulator attachment angles. Material: body - galvanized ductile iron or galvanized steel.

Features

Type YPC yoke plates may be furnished in a variety of sizes, hole spacing, ultimate strengths and insulator attachment angles. Material: Galvanized Ductile Iron

General

Catalog Number	YPC509378
EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	YPC Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359344780

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator	1.25 in
Attachment Holes	
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in

Insulator Throat Diameter - Minimum	0 in
Length - Coupling	12.44 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	30.38 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing Diameter - Conductor Attachment Holes	0 in
	1.25 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	72
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - YPC509378](#)