

Yoke Plate, Triangular

By ANDERSON
Catalog # [YPD40183424](#)

"Vertical Bundling Yoke, Yoke Opening: 3.313", Bottom Width: 1.750", Diameter of Clevis Bolt: 0.625", UTS 15,000 lb"



Features

- "Material: Galvanized Ductile Iron"

General

EU RoHS Indicator	No
Material	Ductile Iron
Series	YPD Series
Strength Rating - Ultimate	40000 lb
UPC	096359344957

Dimensions

Base Hole Spacing	18 in
Diameter - Apex Hole	1.25 in
Diameter - Base Holes	1.25 in
Dimensions	20.75 in x 6.56 in x 2 in
Height	2 in
Insulator / Conductor Hole Spacing	18 in
Length	20.75 in
Length - Coupling	3.625 in
Thickness at Apex	0.75 in
Thickness at Base	0.75 in
Weight	12.985 lb
Width	6.56 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Sales Drawings - YPD40183424 CUTSHEET](#)