

Yoke Plate, Rectangular

By ANDERSON
Catalog # [YPR6019401](#)

Yoke Plate, Rectangular, Ductile Iron, Galvanized, UTS 60,000 lb, 0.94" dia. Holes (8 places)



Features

- "Material: Galvanized Ductile Iron"

General

Corona Ring Mounting Provision	4 x 0.500" -13 UNC Tapped holes
EU RoHS Indicator	No
Material	Ductile Iron
Series	YPR Series
Strength Rating - Ultimate	60000 lb
UPC	096359345312

Dimensions

Diameter - Insulator Attachment Holes	0.938 in
Dimensions	21 in x 9 in x 0.75 in
Height	0.75 in
Insulator / Conductor Hole Spacing	18 in
Length	21 in
Length - Coupling	6 in
Thickness	0.75 in
Weight	24.5 lb
Width	9 in

Conductor Related

Diameter - Conductor Attachment Holes	0.938 in
---------------------------------------	----------

Logistics

Pallet Quantity	80
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Sales Drawings - YPR-60-19401 CUTSHEET](#)