



2.4/5/6 GHZ 13 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-03285 (ATS-OP-2456-13-6RPSP-36)



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
Gain: 9/11/11 dBi
Polarization: Vertical
Horizontal Beamwidth: 30°/15°/12°
Vertical Beamwidth: 120°/110°/110°
VSWR: <2.5



MECHANICAL SPECIFICATIONS

Dimensions: 19.3" x 19.3" x 2.44" (490x490x62mm)
Weight: 2.2 lb (4 kg)
Installation: Flush Mount to Wall or articulating mount (included)

Radome Material: ASA
Connector: RPSMA
Number of Leads: 6
Cable Length: 36" (910mm)
Cable Type: ATS-200



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor
IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL

