





The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Part Number: ATS-12106P-S-L-NH-UBPTB



MECHANICAL SPECIFICATIONS

Size: 12" H x 10" W x 6" D (304.8 mm H x 254 mm W x 152.4 mm D)

Weight: 6.2 lbs (2.81 kg) Color: Light Grey

Material: Polycarbonate

Door Type: Solid

Lock Type: Latch with Integrated Pad Lockable Hasp

Antenna Connection Holes: 0

Hole Size: None Cord Grip: No

Equipment Installation: Universal Backplate and T-Bar

Enclosure Installation: Mounting Feet



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Environmental Protection: NEMA 6P, 4X, 4, 3R, 122; IP68 Operating Temperature: -20 to 240°F (-28 to 115°C)



WARRANTY

2 Year Limited Warranty