



## 14X12X6 POLYCARBONATE ENCLOSURE WITH CLEAR DOOR, KEY LOCK AND NO HOLES



The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Part Number: ATS-14126P-C-K-NH-UBPTB



### MECHANICAL SPECIFICATIONS

Size: 14" H x 12" W x 6" D (355.6 mm H x 304.8 mm W x 152.4 mm D)

Weight: 8.0 lbs (3.63 kg)

Color: Light Grey

Material: Polycarbonate

Door Type: Clear

Lock Type: Key Lock Plus Latch with Integrated Pad Lockable Hasp

Antenna Connection Holes: 0

Hole Size: None

Cord Grip: No

Equipment Installation: Universal Backplate and T-Bar

Enclosure Installation: Mounting Feet



### ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Environmental Protection: NEMA 6P, 4X, 4, 3R, 122; IP68

Operating Temperature: -20 to 240°F (-28 to 115°C)

### WARRANTY



2 Year Limited Warranty