

14X12X6 POE HEATED ENCLOSURE FOR 4 ELEMENT RPTNC EXTERNAL ANTENNA ATS-14126P-S-L-4T-CG-POE-H

HEATED ENCLOSURE SYSTEM COMPONENTS

- 14x12x6in. Polycarbonate Enclosure with Solid Door and Latch Lock
- Ethernet Surge Suppressor for 802.3af/at/bt
- 60W PoE Injector and Line Cord (UPOE & 802.3af/at)
- 12VDC 15W Heater
- DC Adjustable Thermostat (Fahrenheit)
- Ethernet Cable (For AP, Customer provides Ethernet to Enclosure Suppressor)
- Ethernet Surge Suppressor Pre-Wired to Ground
- IP68 Rated Cord Grip
- Blank Backplate provides 10x10¹/₂" Mounting Area *Recommend ¹/₂" self-tap screws*
- 10" DIN Rail
- 7-Port Enclosure Termination Ground Bar
- Ground Lug Assembly with 1/4" Ring Terminal Connection Point
- RPTNC Bulkhead Jack to Plug Lighting Arrestors (4)
- RPTNC Jack to RPTNC Plug Cable Assemblies (4)
- Right Angle RPTNC Jack to RPTNC Plug Adapters (4)

ETHERNET SURGE SUPPRESSOR SPECIFICATIONS

Connector: RJ-45 Jack Operating Voltage: Data 5V, PoE 48V Data Rate (PoE Use Case): 1G/5Gbps Clamping Voltage: 70V Maximum surge discharge current: 10KA (8 to 20uS) Peak pulse current: 100A (10 to 1,000uS) Impulse protected voltage: <650V Response time: <5nS

POE INJECTOR SPECIFICATIONS

Operating Temperature: -40°F to 140°F (-40°C to 60°C) Input Voltage: 120/230 VAC Output Voltage: 56V Output Wattage: 60W Max (802.3af/at or UPoE)

SYSTEM SPECIFICATIONS

Operating Temperature: -4°F to 140°F (-20°C to 60°C) Data Rate: 1 Gbps

WARRANTY

1 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2021 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM










14X12X6 POE HEATED ENCLOSURE FOR 4 ELEMENT RPTNC EXTERNAL ANTENNA ATS-14126P-S-L-4T-CG-POE-H

MECHANICAL SPECIFICATIONS

Size: 14.6" H x 12" W x 6" D (370.84 mm H x 304.8mm W x 152.4 mm D) Weight: 11.7lb (5.3kg) Color: Light Grey Material: Polycarbonate Door Type: Solid Lock Type: Latch with Integrated Pad Lockable Hasp Enclosure Surface Installation: Mounting Feet Included Enclosure Pole Mount Installation: Requires ATS-10P-12P-PMK Pole Mount Kit



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2021 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM