



60 WATT UPOE INJECTOR WITH PSE

The AccelTex Solutions UPOE Injector converts AC line voltage into PoE and includes built in over voltage, over current and short circuit protection. Each injector ships with an AC line cord with US plug and can be flush mounted or DIN rail mounted.

Part Number: ATS-60W-UPOE-INJ

\$

MECHANICAL SPECIFICATIONS

Dimensions: 4.92" L x 2.83" W x 1.49" H (125 mm L x 72 mm W x 38 mm H) Installation: Surface Mount and DIN Rail Clips Included Connector: 2 RJ-45 Jacks

4

ELECTRICAL SPECIFICATIONS

Input Voltage: 120/230 VAC Input Current: 1.03 Amps at 120 VAC, 0.63 Amps at 230 VAC Inrush Current: 25 Amps max at 120 VAC, 50 Amps max at 230 VAC Output Voltage: 56 V Output Wattage: 60 W Max (UPoE) Max Load: 1.07 Amps



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor Operating Temperature: -40 to 140°F (-40 to 60°C) Storage Temperature: -40 to 185°F (-40 to 85°C) Operating Humidity: 5% to 90% RH (non-condensing)



RJ-45 PINOUTS

RJ-45 Input (Data Only)

Data Pair A+ Pin 1 Pin 2 Data Pair A-Pin 3 Data Pair B+ Pin 4 Data Pair C+ Pin 5 Data Pair C-Pin 6 Data Pair B-Pin 7 Data Pair D+ Pin 8 Data Pair D-

\mathbf{Q}

LED INDICATORS

Red: Power Ready Green: PoE Output ok

RJ-45 Output (Data and Power)

Power (-) and Data Pair A+ Pin 1 Pin 2 Power (-) and Data Pair A-Pin 3 Power (+) and Data Pair B+ Power (+) and Data Pair C+ Pin 4 Pin 5 Power (+) and Data Pair C-Pin 6 Power (+) and Data Pair B-Pin 7 Power (-) and Data Pair D+ Pin 8 Power (-) and Data Pair D-

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2018 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM