

65W 802.3AF/AT OUTDOOR POE INJECTOR ATS-65W-OD-POE-INJ



MECHANICAL SPECIFICATIONS

Dimensions: 11.02" x 8.07" x 3.15" (280 x205 x 80mm)

Shell Material: IP65 Grade Aluminum

IP65 Ports: 2 RJ-45 Jacks (LAN and PoE)

1 AC Input Port 1 DC Input Port



ELECTRICAL SPECIFICATIONS

AC Input Voltage: 100-265VAC 50-60Hz

DC Input Voltage: 50-57VDC PoE Output Voltage: 55V PoE Standard: IEEE 802.3af/at

Power Pin Assignment: 1/2(-), 3/6(+) and 4/5(+), 7/8(-)

Data Rate: 10/100/1000 Mbps

EMI Protection: IEC 61000-4-2, IEC61000-4-5



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40°F to 185°F (-40°C to 85°C) Storage Temperature: -49°F to 185°F (-45°C to 85°C) Operating Humidity: 10% to 90% RH (Non-condensing)

Weather Rating: IP65





