



### MECHANICAL SPECIFICATIONS

Dimensions: 7.17" x 2.83" x 1.38" (182 x 72 x 35mm)  
Connector: 2 RJ-45 Jacks  
LAN Port: 1G, 2.5G, 5G, 10G



### ELECTRICAL SPECIFICATIONS

AC Input Voltage: 100-240VAC 50/60Hz  
PoE Output Voltage: 52VDC 1.75A  
Output Wattage: 90 Watts  
Pinout: 1,2+/ 4,5+ and 3,6-/ 7,8-  
Regulatory: UL62368-1:2014+A11:2017, FCC Part 15 Class B, EN 55032:2015, EN 61000-32:2019, EN 61000-3-3:2013+A1:2019, EN 55035:2017, EN 62368-1:2014+A11:2017  
\*Comes with U.S. Line Cord\*



### ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor  
Operating Temperature: -13°F to 140°F (-25°C to 60°C)  
Storage Temperature: -40°F to 176°F (-40°C to 80°C)  
Operating Humidity: 10% to 90% RH (Non-condensing)