



MOUNT V3 - BLACK ATS-APANTARTMNT-UNIV3-BLK



FEATURES

- Special insert holes for APs that use DART cables
- Universal design to accommodate different manufacturer APs
- Maximum horizontal and vertical antenna articulation
- Includes clear degree markings for precise angling of the antenna
- Powder-coated finish for indoor or outdoor installation
- Lengthening arms can be used to acquire maximum articulation or can be removed for a more compact installation
- Aruba mounting hole pattern has been added to all included mounting plates for better compatibility with newer Aruba APs
- All-thread mounting bracket has been redesigned to enhance mounting security and safety
- * An AP safety tether is recommended







BENEFITS

- Easy to install
- Versatile compact design
- Variety of mounting options including beam clamps, 3/8" All-Thread, flush-wall or ceiling mount
- Simple, one-person installation
- Future proof install a new AP or antenna instantly



MOUNT SHIPS WITH

- (2) Beam Clamps
- (1) Long TBAR Mounting plate



MECHANICAL SPECIFICATIONS

Dimensions: 10.9"L x 8.3"W x 10.5" H (277 x 210 x 266mm)

Weight: 5.05 lbs. (2.29 kg)

Color: Black

Installation: Wall, Ceiling, I-Beam, 3/8" All-Thread Mount, Metal Strapping

Short Arm Max Articulation: ±60° depending on AP Height

Long Arm Max Articulation: ±35° for Antennas 8" or larger / ±45° for Antennas smaller than 8"

*Max angles vary when both articulation points are used along with the AP size. Taller AP may not allow for full articulation



ENVIRONMENTAL SPECIFICATIONS

WARRANTY

Installation Environment: Indoor or Outdoor

1 Year Limited Warranty



COMPATIBLE APS

The same APs as our ATS-APANTARTMNT-UNIV3 regular model.





UNIVERSAL AP AND ANTENNA ARTICULATING **MOUNT V3 - BLACK ATS-APANTARTMNT-UNIV3-BLK**







