



12x10x6 Polycarbonate Enclosure with Clear Door, Latch Lock & 6 N-Style Holes

By AccelTex Solutions
Catalog # [ATS-00080](#)



ATS-00080 (former catalog number ATS-12106P-C-L-6N-CG-UBPTB). The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Features

- Polycarbonate enclosure protects enterprise-class APs from environmental threats and tampering
- Provides NEMA-rated durability for outdoor use and a discreet design for indoor applications

Application

Indoor Wi-Fi, Outdoor Wi-Fi

General

Catalog Number	ATS-00080
Color	Light Grey
Compatibility	<ul style="list-style-type: none">• Arista O-235E• Aruba/HP AP-574• Cisco Catalyst 9124AXE• Mist AP63E
Compatibility Hole Size	N-Style
Cord Grip	Yes
Door Type	Clear
Enclosure Style	Mounting Feet
Indoor/Outdoor	Indoor or Outdoor

Installation Type	Universal Backplate and T-Bar
Lock Type	Latch
Material	Polycarbonate
Number Of Antenna	6
Connection Holes	
Operating Temperature	-28 to 115 °C
Technology	802.11ac, 802.11ax, 802.11n, 802.3af, 802.3at
UPC	662620431529

Dimensions

Dimensions	12 in x 10 in x 6 in
Height	6 in
Length	12 in
Width	10 in

Certifications And Compliance

Ratings	122
---------	-----

Product Assets

[Sales Drawings - Outline Drawing](#)
[Specifications - Specification Sheet](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
ATS-ATS00080-SPEC-EN | REV 4/2025