



12x10x6 Polycarbonate Enclosure with Clear Door, Latch Lock & Cord Grip

By AccelTex Solutions
Catalog # [ATS-00090](#)



ATS-00090 (former catalog number ATS-12106P-C-L-CG-UBPTB). The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Features

- Polycarbonate enclosure protects enterprise-class APs from environmental threats and tampering
- Provides NEMA-rated durability for outdoor use and a discreet design for indoor applications

Application

Indoor Wi-Fi, Outdoor Wi-Fi

General

| | |
|----------------|---|
| Catalog Number | ATS-00090 |
| Color | Light Grey |
| Compatibility | <ul style="list-style-type: none">• Arista C-230• Arista C-230E• Arista C-330• Arista C-360• Arista C-460• Arista C-460E• Arista O-105E• Arista O-235• Arista O-235E• Aruba/HP AP-504• Aruba/HP AP-505• Aruba/HP AP-514• Aruba/HP AP-515• Aruba/HP AP-518• Aruba/HP AP-534• Aruba/HP AP-535• Aruba/HP AP-565• Aruba/HP AP-567• Aruba/HP AP-615• Aruba/HP AP-635• Aruba/HP AP-735• Cisco 1562e• Cisco Catalyst 9105AXI• Cisco Catalyst 9115i• Cisco Catalyst 9115e |

| | |
|-----------------------|--|
| | <ul style="list-style-type: none">• Cisco Catalyst 9120AXI• Cisco Catalyst 9120AXE• Cisco Catalyst 9120AXP• Cisco Catalyst 9124AXD• Cisco Catalyst 9124AXE• Cisco Catalyst 9124AXI• Cisco Catalyst 9130AXE• Cisco Catalyst 9130AXI• Mist AP24• Mist AP32• Mist AP32e• Mist AP33• Mist AP34• Mist AP43• Mist AP43e• Mist AP45• Mist AP45E |
| Cord Grip | Yes |
| Door Type | Clear |
| Enclosure Style | Mounting Feet |
| Indoor/Outdoor | Indoor or Outdoor |
| Installation Type | Universal Backplate and T-Bar |
| Lock Type | Latch |
| Material | Polycarbonate |
| Operating Temperature | -28 to 115 °C |
| Technology | 802.11ac, 802.11ax, 802.11n, 802.3af, 802.3at |
| UPC | 662620431581 |

Dimensions

| | |
|------------|----------------------|
| Dimensions | 12 in x 10 in x 6 in |
| Height | 6 in |
| Length | 12 in |
| Width | 10 in |

Certifications And Compliance

| | |
|---------|-----|
| Ratings | 122 |
|---------|-----|



A Hubbell brand