



## 14x12x6 Heated & Cooled PoE Enclosure for 4 Element N-Style External Antenna

By AccelTex Solutions  
Catalog # [ATS-00240](#)



ATS-00240 (former catalog number ATS-14126P-S-L-4N-CG-POE-HC). The AccelTex Solutions Heated & Cooled PoE enclosure allows an access point to be installed in an outdoor or other temperature-limiting environment. The heater, fan and AP are all powered by a single PoE cable run from the network switch. The enclosure ships ready for an AP and external antenna installation. This version is for a 4-Element N-Style External Antenna.

### Features

- Features both heating and cooling elements to protect equipment
- Pre-configured and pre-drilled holes for 4-Element N-Style External antennas
- Power heater, fan, and AP through a single PoE cable for outdoor applications
- The enclosure system components include:
  - 14x12x6 polycarbonate enclosure with solid door and latch lock
  - Ethernet surge suppressor for 802.3at/af/bt
  - 60W PoE Injector and Line Cord (UPOE & 802.3at/af Type 3)
  - 12VDC 15W Heater and 3" Fan
  - DC Adjustable Thermostat (Fahrenheit)
  - Ethernet Cable (For AP. Customer provides Ethernet to enclosure suppressor)
  - Ethernet Surge Suppressor pre-wired to ground
  - IP68 Rated Cord Grip
  - Blank backplate provides 10"x10.5" mounting area (Recommend 1/2" self-tap screws)
  - Vents
  - 10" DIN rail
  - Dual-Layered Fan Filter
  - 7-Port Enclosure Termination Ground Bar
  - Ground Lug Assembly with 1/4" Ring Terminal Connection Point
  - N-Style Bulkhead Jack to Plug Lightning Arrestors (4)
  - N-Style Jack to N-Style Plug Cable Assemblies (4)
  - Right-Angle N-Style Jack to N-Style Plug Adapters (4)

### Application

Indoor Wi-Fi, Outdoor Wi-Fi

### General

Catalog Number      ATS-00240  
Color                      Grey

### Compatibility

Compatibility Hole Size

Cord Grip

Door Type

Enclosure Size

Enclosure Style

Enclosure System Components

• Cisco MR76

• Cisco MR86

N-Style

Yes

Solid

14x12x6

Mounting Feet

14"x12"x6" Poly Enclosure with Solid Door, customer-provides-ethernet-to-enclosure-suppressorethernet-surge-suppressor-pre-wired-to-groundip68-rated-cord-gripblank-backplatevents10-din-raildual-layered-fan-filter7-port-enclosure-term, latch-lockethernet-surge-suppressor-for-802-3at-af-bt-type-360w-poe-injector-and-line-cord-upoe-802-3at-af-bt-type-312-vdc-15w-heater-and-3-fandc-adjustable-thermostat-fahrenheitethern

Heated & Cooled

Indoor or Outdoor

Latch

Polycarbonate

4

Environmental Conditions

Indoor/Outdoor

Lock Type

Material

Number Of Antenna

Connection Holes

Operating Temperature

Technology

-20 to 60 °C

802.11ac, 802.11ax, 802.11n,

802.3af, 802.3at

662620432427

UPC

### Dimensions

Dimensions


Height

14 in x 12 in x 6 in

6 in

Length14 in  
Width12 in

Product Assets  
[Specifications - Specification Sheet](#)



©2025 Hubbell Incorporated. All rights reserved  
ATS-ATS00240-SPEC-EN | REV 4/2025