



60 Watt PoE Injector and Line Cord (802.3af and 802.3at)

By AccelTex Solutions
Catalog # [ATS-00445](#)



ATS-00445 (former catalog number ATS-60W-POE-INJ). The AccelTex Solutions PoE Injector converts AC line voltage into PoE and includes built in over voltage, over current and short circuit protection. Each injector ships with an AC line cord with US plug and can be flush mounted or DIN rail mounted.

Features

- Converts AC lines voltage into PoE with integrated over-voltage, over-current, and short-circuit protection
- Includes AC line cord (US plug) and supports flush or DIN rail mounting

Application

Carpeted Space, Energy/Facility Management, High Density, Indoor Wi-Fi, Outdoor Wi-Fi, Stadium

General

Catalog Number	ATS-00445
Connector Type	(2) RJ-45 Jacks
Indoor/Outdoor	Indoor
Input	0.63 Amps at 230 VAC, 1.03 Amps at 120 VAC
Installation Type	Surface Mount and DIN Rail Clips

Operating Temperature	-25 to 50 °C
Storage Temperature Range	'-40 to 185 F (-40 to 85 C)
Technology	802.3af, 802.3at
UPC	662620433929

Dimensions

Dimensions	4.9 in x 2.8 in x 1.5 in
Height	1.5 in
Length	4.9 in
Width	2.8 in

Electrical Ratings

Load Current Maximum	1.07 A
Operating Voltage	120/230 VAC
Output Voltage	56 V
Wattage - Maximum	60 W

Product Assets

[Specifications - Specification Sheet](#)