



65 Watt 10/100/1000 Outdoor PoE Injector (802.3af/at)

By AccelTex Solutions
Catalog # [ATS-00448](#)

ATS-00448 (former catalog number ATS-65W-OD-POE-INJ). The ATS-00448 is a dependable outdoor single port midspan solution that supports 802.3af/at powered devices. It can be powered using DC or AC voltage and comes with built in surge protection. All ports utilize IP65 rated connectors.

Features

- Outdoor PoE injector supports 802.3af/at standards with DC or AC power input
- Features built-in surge protection and IP65-rated connectors

Application

Energy/Facility Management, High Density, Indoor Wi-Fi, Outdoor Wi-Fi, Stadium

General

Catalog Number	ATS-00448
Connector Type	(2) RJ-45 Jacks (1) AC Input Port (1) DC Input Port
Humidity	10% to 90% RH (non-condensing)
Indoor/Outdoor	Indoor or Outdoor
Input	57VDC;AC 100-240V 50/60HZ



Installation Type	Pole Mount
Operating Temperature	-40 to 85 °C
Storage Temperature Range	'-40 to 185 F (-40 to 85 C)
Technology	802.11ax, 802.3af, 802.3at
UPC	662620433943

Dimensions

Dimensions	11.02 in x 8.07 in x 3.15 in
Height	3.15 in
Length	11.02 in
Width	8.07 in

Electrical Ratings

Output Voltage	52 VDC
----------------	--------

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand