



2.4/5 GHz 2/3 dBi White Indoor Stubby Duck Antenna w/RPTNC

By AccelTex Solutions
Catalog # [ATS-00857](#)



ATS-00857 (former catalog number ATS-IDSD-245-23-1RPTP-IC). The AccelTex Solutions dual band indoor stubby duck antenna is a perfect compliment to any enterprise-class AP to achieve desired coverage in your indoor space. The antenna element is optimized for Wi-Fi operation on both 2.4 and 5 GHz and attaches directly to any enterprise-class AP. This highly versatile antenna is suitable for a broad range of indoor applications where a higher gain external antenna is not needed.

Features

- Dual band indoor stubby duck antenna optimized for 2.4 and 5 GHz Wi-Fi
- Compact design attaches directly to enterprise-class APs.

Application

Indoor Wi-Fi

General

Antenna Gain	2/3 dBi
Antenna Type	Omni
Beamwidth - Horizontal	360°
Beamwidth - Vertical	144°/95°
Catalog Number	ATS-00857
Compatibility	<ul style="list-style-type: none">• Cisco Catalyst 9115e• Cisco Catalyst 9120AXE• Cisco MR46E
Connector Type	RPTNC Plug

Indoor/Outdoor	Indoor
Installation Type	Direct Connect to Radio
Number of Leads	1
Polarization	Vertical
Technology	802.11ac, 802.11ax, 802.11n
UPC	662620435152

Dimensions

Height	0 in
Length	2 in
Width	0.8 in

Electrical Ratings

Frequency Rating	2.4-2.5/4.9-5.85 GHz
Impedance	50 Ohms
Voltage Ratio	≤2.0

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand