



2.4/5 GHz 5/7 dBi White Indoor/Outdoor Omni Antenna w/N-Style

By AccelTex Solutions
Catalog # [ATS-01057](#)

ATS-01057 (former catalog number ATS-OO-245-57-1NP-IC-W).
The AccelTex Solutions Dual-Band 5/7 dBi ABS omnidirectional antenna is designed for indoor and outdoor environments in the 2.4GHz and 5GHz wireless local area networks.

Features

- Dual band ABS omnidirectional antenna (5/7 dBi) for 2.4 GHz and 5 GHz Wi-Fi
- Ideal for indoor and outdoor wireless local area networks

Application

Outdoor Wi-Fi

General

Antenna Gain	5/7 dBi
Antenna Type	Omni
Beamwidth - Horizontal	360°
Beamwidth - Vertical	30°/20°
Catalog Number	ATS-01057
Compatibility	<ul style="list-style-type: none">• Arista O-235E• Aruba/HP AP-574• Aruba/HP AP-584• Cisco 1572eac• Cisco 1572ec• Cisco MR76• Cisco MR86• Mist AP63E

Connector Type	N-Style Plug
Indoor/Outdoor	Outdoor
Input Power - Max	20W
Material - Radome	ABS
Number of Leads	1
Operating Temperature	-40 to 60 °C
Polarization	Vertical
Technology	802.11ac, 802.11ax, 802.11n
UPC	662620435718

Dimensions

Height	0 in
Length	10.7 in
Width	0.9 in

Electrical Ratings

Frequency Rating	2.4-2.5/5.1-5.9 GHz
Impedance	50 Ohms
Voltage Ratio	≤2

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand