

2.4/5 GHZ 2/3.5 DBI WHITE OMNI STUBBY ANTENNA WITH N-STYLE PLUG ATS-IDSD-245-23-1NP-IC



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5 / 4.9-5.85 GHz

Gain: 2 / 3.5 dBi VSWR: ≤2.0



MECHANICAL SPECIFICATIONS

Dimensions: 1.93"x 0.75" (49mm x 19mm)

Radome Material: ABS Connector: N-Style Plug Flammability Class: UL-94 HB






ENVIRONMENTAL SPECIFICATIONS

WARRANTY

Installation Environment: Indoor/Outdoor

IP Rating: IP 66

2 Year Limited Warranty







2.4/5 GHZ 2/3.5 DBI WHITE OMNI STUBBY ANTENNA WITH N-STYLE PLUG ATS-IDSD-245-23-1NP-IC



2.4 GHZ







3

2.45 GHZ

H-Plane

E-Plane







H-Plane

E-Plane



2.5 **GHZ**








2.4/5 GHZ 2/3.5 DBI WHITE OMNI STUBBY ANTENNA WITH N-STYLE PLUG ATS-IDSD-245-23-1NP-IC



4.9 GHZ




180 E-Plane




5.4 GHZ

H-Plane




H-Plane




E-Plane



5.8 GHZ



H-Plane



E-Plane