

2.4/5 GHZ 4 DBI 8 ELEMENT INDOOR/OUTDOOR DUAL DIRECTIONAL HANDRAIL PATCH ANTENNA WITH RPSMA ATS-ODDHRP-245-4-8RPSP-120

4

ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5/4.9-5.85 GHz Gain: 4 dBi Polarization: Vertical Horizontal Beamwidth: 117°/110° Vertical Beamwidth: 81°/78°

VSWR: <2.2:1 Impedance: 50 Ω Isolation: >20 dB Lightning Protection: DC Grounded Max Input Power: 100W



\$

MECHANICAL SPECIFICATIONS


Dimensions: 7.9" L x 5.9" H x 2.2" D (201.83 mm L x 150 mm H x 55mm D) Weight: 1.2 lb (0.5 kg) Installation: 3 Handrail Adapters Pole Mount Diameter: Up to 2" Pole (50.8 mm) diameter Radome Material: ASA Connector: RPSMA Plug Number of Leads: 8 Cable Length: 10' (3048 mm) Cable Type: RG58

0

ENVIRONMENTAL SPECIFICATIONS


Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 149°F (-40 to 65°C) Wind Velocity: 130 mph (210 km/h) IP Rating: IP66

2.4 GHZ



WARRANTY

2 Year Limited Warranty



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.