

2.4/5 GHZ 10/11 DBI 4 ELEMENT INDOOR/OUTDOOR HIGH DENSITY PATCH ANTENNA WITH N-STYLE ATS-OHDP-245-1011-4NJ-IC



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5/4.9-5.85 GHz

Gain: 10/11 dBi

Polarization: 2 Vertical, 2 Horizontal Horizontal Beamwidth: 55°/40° Vertical Beamwidth: 55°/50°

VSWR: ≤2.0:1 Isolation: >20 dB Impedance: 50 Ω Lightning Protection: DC Grounded

Max Input Power: 100W





MECHANICAL SPECIFICATIONS

Dimensions: 9.1"x 9.1"x 1.8" (230x230x45mm)

Weight: 1.3 lb (0.6 kg)

Installation: Articulating Wall/Pole Mount (included)

Pole Mount Diameter: 2" (50mm)

Connector: N-Style Jack (Note: Cable assemblies not included. View https://www.acceltex.com/product-category/cable-

assemblies/n-style-to-n-style-cable-assemblies/n-style-plug-to-n-style-plug/)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 149°F (-40 to 65°C)

Wind Velocity: 130 mph (210 km/h)

IP Rating: IP66

WARRANTY

2 Year Limited Warranty

Radome Material: ASA

Number of Leads: 4 (Integrated)



2.5 GHZ

5.5 GHZ

