

# 2.4/5 GHZ 4/4 DBI 4 ELEMENT INDOOR/OUTDOOR 90°/90° HD PATCH ANTENNA WITH RPSMA ATS-OHDP-245-4-4RPSP-36



## **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.5/4.9-5.85 GHz

Gain: 4 / 4 dBi

Polarization: 2 Horizontal - 2 Vertical Horizontal Beamwidth: 90°/90° Vertical Beamwidth: 90°/90°

VSWR: < 2





## **MECHANICAL SPECIFICATIONS**

Dimensions: 11"x 5.9"x 1.97" (280x150x50mm)

Weight: 2.2 lb (0.99 kg)

Mounting: Threaded Center Bolt w/ Nut & Articulating Wall/Pole Mount (included) Installation Hole Diameter: 1" (25mm) Pole Mount Diameter: 2" (508mm)

Radome Material: ASA Connector: RPSMA Number of Leads: 4

Cable Length: 36" (910 mm) Cable Type: ATS-195



# **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 149°F (-40 to 65°C)

Wind Velocity: 130 mph (209 km/h)

IP Rating: IP66


#### **WARRANTY**


2 Year Limited Warranty



## **HORIZONTAL**

# **VERTICAL**







# 2.4/5 GHZ 4/4 DBI 4 ELEMENT INDOOR/OUTDOOR 90°/90° HD PATCH ANTENNA WITH RPSMA ATS-OHDP-245-4-4RPSP-36

