



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
 Gain: 12/12/12 dBi
 Polarization: Vertical and Horizontal
 Horizontal Beamwidth: 35°/30°/30°
 Vertical Beamwidth: 35°/30°/30°
 VSWR: <2



MECHANICAL SPECIFICATIONS

Dimensions: 19.3" x 19.3" x 2.44" (490x490x62mm)
 Weight: 2.2 lb (4 kg)
 Installation: Flush Mount to Wall or Articulation Mount

Radome Material: ASA
 Connector: RPSMA
 Number of Leads: 8
 Cable Length: 36" (910mm)
 Cable Type: ATS-195



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor
 IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL



