

2.4/5 GHZ 2/3.5 DBI OUTDOOR OMNI ANTENNA WITH N-STYLE PLUG ATS-OO-245-37-1NP-IC-W



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.484 / 5.1-5.85 GHz

Gain: 3 / 7 dBi
Polarization: Vertical
Horizontal Beamwidth: 360°
Vertical Beamwidth: 50° / 30°

VSWR: ≤2.84 / ≤1.49



MECHANICAL SPECIFICATIONS

Dimensions: 10.8" L (27.5cm) Weight: 0.33 lb (0.15 kg)

Ingress Protection: Outdoor IP65

Radome Material: Fiberglass Connector: N-Style Plug



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40°F to 140° F (-40° C to 60° C)

IP Rating: IP 66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL



