

2.4/5 GHZ 4.5/5 DBI OUTDOOR OMNI ANTENNA WITH N-STYLE PLUG ATS-00-245-45-1NP-IC-W



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-5 GHz / 5.35—5.9 GHz Gain: 4.5 / 5 dBi Polarization: Vertical Horizontal Beamwidth: 360° Vertical Beamwidth: 30° / 25°



MECHANICAL SPECIFICATIONS


Dimensions: 9.5" L x 0.86" DIA (140*22mm) Weight: 0.9 lb (0.4 kg) Ingress Protection: Outdoor IP65

ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -32 to 158° F (-40 to 70 °C) IP Rating: IP 66



HORIZONTAL




VSWR: ≤2 Isolation: >18 dB Impedance: 50 Ω Lightning Protection: DC ground Max Input Power: 20 W

Radome Material: Fiberglass Connector: N-Style Plug

WARRANTY

2 Year Limited Warranty

VERTICAL



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2023 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM